



MONO TESTA TERMICA
ONE HEAD HEATING



FIXY 2400

Applicazione strass su tessuto





MONO TESTA TERMICA

ONE HEAD HEATING

FIXY 2400

Applicazione strass su tessuto



La macchina FIXY 2400 Monotesta Termica permette l'applicazione di strass e/o borchie termoadesive su tessuti di qualsiasi tipo. L'applicazione di strass termoadesivi con FIXY 2400 puo' essere effettuata su capi di qualsiasi tipo, magliette, jeans, pantaloni, maglie, giubbotti e tanti altri impreziosendone la sua immagine limitatamente allo spessore del capo.

FIXY 2400 Monotesta Termica disponendo di un solo caricatore consente l'applicazione di un solo tipo di strass per ciclo di lavorazione.

FIXY 2400 si differenzia per le seguenti caratteristiche:

- 1 . Prelevamento centrato grazie al sistema stepping rotation, grazie al quale si posiziona lo strass e/o
- 2 . Alta velocita' di lavorazione : max 3000 pezzi/ora
- 3 . Elavata affidabilita', garantita dall'impiego di componenti di altissima qualita'.
- 4 . Modalita' " pressing " utilizzando FIXY 2400 come piccola pressa per poter applicare piccole cartine a transfer senza danneggiare i tessuti sintetici come sulle tradizionali termopresse.

FIXY 2400 One Head Heating allows hot fix rhinestones and/or nailheads to be applied to any type of fabric.

Hot fix rhinestones can be applied on any garment using FIXY 2400, adorning them: T-shirts, jeans, pants, sweaters, jackets, and many others, adding a precious touch to the image on the basis of the thickness of the garment.

With the single loader FIXY 2400 One Head Heating is able to apply one style of rhinestone at a time for each work cycle.

FIXY 2400 stands out thanks to the following features:

- 1 . Centred withdrawal thanks to the stepping rotation system; this system positions the rhinestone and/or nailhead on the garment in the correct position for setting without breaking or squishing it.
- 2 . High processing speed: Max. 3,000 pieces/hour.
- 3 . High reliability, guaranteed by the use of only high quality components.
- 4 . "Press" mode for using FIXY 2400 as a small press for the application of small transfers without the risk of damaging synthetic fabrics, as is encountered with traditional hot presses.

CARATTERISTICHE TECNICHE / TECHNICAL FEATURES

ACCESSORI APPLICABILI

ACCESSORIES APPLICABLE

Strass / Rhinestones

SS5 - SS6 - SS8 - SS10 - SS12 - SS16 - SS20
SS30 - SS34 - SS40

Borchie piatte / Nailhead round	mm	2 . 3 . 4 . 5 . 6 . 8
Borchie sfaccettate / Octagon	mm	2 . 3 . 4 . 5 . 6
Borchie cupola / Half round	mm	2 . 3 . 4 . 5 . 6 . 8
Cabochn plastica / Epoxy pearl	mm	2 . 3 . 4 . 5 . 6 . 8
Cabochn vetro / Cat'Eye	mm	4 . 6 . 7
Mezze perle / Half pearl	mm	2 . 3 . 4 . 5 . 6
Perle cupola / Pearl stud	mm	2 . 3 . 4 . 5 . 6

ALIMENTAZIONE

FEEDING

Volt/hz 220/50-60

DIMENSIONI

DIMENSIONS

cm 70 x 60 x H 117

PESO

WEIGHT

kg 80



G.S.M. s.r.l.
via Campania n°1 _41012 Carpi (MO)

T +39 059 69 96 58
F +39 059 62 29 631

info@gsmfixy.com
www.gsmfixy.com